POWERMATE.

PM2000

Portable Generator

Model P0080900 UPC: 696471080322 (EPA/49 ST/CSA)

Features

- **POWERDIAL™ Recoil Start** (Off/Run/Cold Start) offers three operation settings integrated into one simple-to-use dial.
- Large Capacity Steel Fuel Tank provides durability and up to a 14 hour run-time at 25% load.
- **Powered by Generac 98cc OHV Engine** provides consistent power for multiple applications.
- Ergonomic Frame for easy portability.
- Low-Oil Level Shutdown prevents engine damage.
- Fuel Gauge allows users to keep track of gasoline levels.
- Covered outlets provide protection and keep out debris.



AC Maximum Output Starting Watts 2000 AC Rated Output Running Watts 1400

49-State / CSA Control Panel



POWERMATE.

PM2000

Specifications

Product Series	PM2000
Model (Configuration)	P0080900 (EPA/49 ST/CSA)
AC Maximum Output Starting Watts	2000
AC Rated Output Running Watts	1400
Rated AC Voltage	120 VAC
Rated AC Frequency	60 Hz
Rated 120 VAC Amperage	11.7
Engine Displacement	98cc
Engine Type	OHV
Engine RPM	3600
Recommended Oil	10W-30
Lubrication Method	Splash
Choke Location	Integrated into POWERDIAL™
Fuel Shut Off	On Fuel Tank
Starting Method	Recoil Pull Start
Low Oil Shutdown	Low Level

Floating Neutral	Yes
Start Switch Type	POWERDIAL™
Start Switch Location	On Control Panel
Fuel Tank Capacity Gal (L)	2.25 (8.5)
Run Time at 25% of Rated Load (Hours)	14
Run Time at 50% of Rated Load (Hours)	10
Warranty- Residential	3 Year Ltd
Warranty- Commercial	90 Day

Dimensions and Weights

Length in (mm)	19.7 (500)
Width in (mm)	15.6 (395.5)
Height in (mm)	17 (431.3)
Carton Length in (mm)	20.7 (525)
Carton Width in (mm)	16.9 (430)
Carton Height in (mm)	18.1 (460)
Unit Weight Ibs (kg)	62 (28.1)
Shipping Weight lbs (kg)	68 (30.8)



POWERMATE.

Powermate, LLC • S45 W29290 Hwy 59, Waukesha, WI 53189 • powermate.com ©2020 Powermate, LLC. All rights reserved. All specifications are subject to change without notice. Part No. A0000761866-B 09/29/2020