POWERMATE

PM1200i

Inverter Generator

Model P0080400 UPC: 696471078909 (50 ST)

Features

- Ultra Quiet Performance with fully enclosed case.
- RPM+ automatically adjusts engine RPM based on load demand to reduce sound emissions and conserve fuel.
- Clean, Stable Power with less than 3% total harmonic distortion for safe operation of sensitive electronics.
- 0.8 Gallon Fuel Tank provides a 7 hour run time at 25% load.
- Lightweight Design with built-in handle for easy portability.
- Powermate OHV engine provides consistent power for multiple applications.
- Low-oil level shutdown prevents engine damage.



AC Maximum Output Starting Watts 1200
AC Rated Output Running Watts 1000

Control Panel



POWERMATE.

PM1200i

Specifications

Product Series	PM1200i
Model (Configuration)	P0080400 (50 ST)
AC Maximum Output Starting Watts	1200
AC Rated Output Running Watts	1000
Rated AC Voltage	120 VAC
Rated AC Frequency	60 Hz
Rated 120 VAC Amperage	8.3
Total Harmonic Distortion	Less than 3%
Engine Displacement	54cc
Engine Type	OHV
Engine RPM	Variable
Recommended Oil	10W-30
Lubrication Method	Splash
Choke Location	On Service Panel
Fuel Shut Off	Under Recoil Handle
Starting Method	Recoil Pull Start
Low Oil Shutdown	Low Level
Floating Neutral	Yes

Start Switch Type	Off/Run Knob
Start Switch Location	Under Recoil Handle
Fuel Tank Capacity Gal (L)	0.79 (3.0)
Run Time at 25% of Rated Load (Hours)	7
Run Time at 50% of Rated Load (Hours)	5.5
Warranty- Residential	3 Year Ltd
Warranty- Commercial	90 Days

Dimensions and Weights

Length in (mm)	18.3 (463.6)
Width in (mm)	10.3 (260.8)
Height in (mm)	15.7 (398.4)
Carton Length in (mm)	19.4 (493)
Carton Width in (mm)	11.8 (300)
Carton Height in (mm)	16.3 (415)
Unit Weight lbs (kg)	33 (15)
Shipping Weight lbs (kg)	36.3 (16.5)



