

MAX AP CANOPY

10 x 20 ft. / 3,0 x 6,1 m

RIPSTOP TOUGH FABRIC COVER

Triple-layer woven polyethylene fabric material. Heat-sealed seams for stronger bond and 100% water resistance.

RESISTS THE ELEMENTS

Protects what's underneath from harmful UVA and UVB rays.

HIGH GRADE STEEL FRAME

Heavy duty 1 3/8 in. / 3,5 cm diameter steel frame with premium powder coat finish resists chipping, peeling, rust and corrosion.

PATENTED TWIST-TITE TENSIONING

Patented feature that squares up frames and tightens down covers for a clean and finished look.

QUICK & EASY SET UP

With swedged tubing. Wide foot plates on every leg add stability/easy anchor points.

