

## Lawn Edger

## Residential Power Tools

Model: LER1035GMNG (47-State)  
UPC: 843530007589



## FEATURES

- **Curb hop ability:** 6 in (15.2 cm) curb hopping feature adds versatility to this machine, making edging possible along all driveways.
- **Variable edging depth:** 6-position depth control allows for edging from 0–3 in (0–76 mm).
- **Powerful OHV Generac engine:** Easy-starting 163cc OHV Generac engine offers 6.5 ft-lbs (8.8 Nm) of gross torque.
- **Tri-lobe edging blade:** 9 in (22.9 cm) tri-lobe blade offers versatile edging power and increases the lifespan of the blade.
- **Lateral wheel adjustment:** Front wheels can be positioned anywhere along the axle to stabilize and match the work surface.
- **4-Wheel design:** The 4-wheel design provides greater stability and control.

## Lawn Edger

## Specifications

Engine	
Displacement	163cc
Torque	6.5 ft-lbs (8.8 Nm)
Starting	Manual
Engine speed	3,000 rpm
Bore x stroke	68 mm x 45 mm
Spark plug	Torch F7RTC or equivalent
Construction	
Edger blade	Powder coated steel
Frame	Powder coated steel
Handlebars	Powder coated steel
Edging Details	
Edger blade diameter	9 in (22.8 cm)
Cutting depth	0.0–3.0 in (0.0–76 mm)
Packaging	
Packaging dimensions (in / cm)	30.5 x 19.25 x 19.25 / 77.5 x 48.9 x 48.9
Packing weight (lbs / kg)	85 / 38.6

Unit Dimensions	
Height	39.5 in (100.3 cm)
Width	19 in (48.3 cm)
Length	45 in (114.3 cm)
Wheels	8 in (20.3 cm)
Unit weight	71 lbs (32 kg)
Miscellaneous	
Assembly time required	15 minutes
Controls	Blade engage lever, operator presence control lever
Personal protective equipment required	Eye protection, ear protection
USDA Certified spark arrestor	No
Warranty	2 years limited