(49-State)

GP8000E

GP SERIES Portable Generator

GENERAC®

Model 7675-1 UPC: 696471074550

Features


- COsense® Technology STOPS, ALERTS, SAVES. Powerful protection against hazardous carbon monoxide.
- PowerRush™ Advanced Technology Delivers over 30% more starting capacity allowing you to do more with less.*
- Electric start for easy operation (battery included).
- 25ft Generator Cord Included Plug in more devices with the multi-outlet generator cord.
- Generac's OHV engine with splash lubrication provides a long engine life.
- Low-oil level shutdown automatically safeguards engine from damage.
- Large-capacity steel fuel tank with incorporated fuel gauge provides durability and up to an 11 hour run-time at 50% load.
- 1 1/4" steel-tube cradle for added durability and strength.
- Heavy-duty, never-flat wheels allow for easy portability.
- Fold-down handle for sturdy portability and compact storage.
- HomeLink™ manual transfer switch compatible.

*Increases electrical current upon demand above rated output when starting electric motors.



AC Rated Output Running Watts 8000 AC Maximum Output Starting Watts 10000

Control Panel





GP8000E

GENERAC°

Specifications

Product Series	GP8000E	
Model Number	7675-1	
Configuration	49 State	
AC Rated Output Running Watts	8000	
AC Maximum Output Starting Watts	10000	
Rated AC Voltage	120/240 VAC	
Rated AC Frequency	60 Hz	
Rated 120/240 VAC Amperage	66.6/33.3	
Engine Displacement	420cc	
Engine Type	OHV	
Engine RPM	3600	
Recommended Oil	10W-30 / SAE 30	
Oil Capacity qt (L)	1.06 (1.0)	
Lubrication Method	Splash	
Automatic Voltage Regulation (AVR)	Yes	
Choke Location	On Engine	
Fuel Shut Off	On Fuel Tank	
Starting Method	Electric Start / Recoil Pull Start	
Battery Included	Yes	
Battery Type	Sealed, Lead Acid (12V DC, 9Ah)	

Battery Part No.	0G9449
Battery Dimensions	5.94" x 2.56" x 3.70"
Battery Wall Charger Adapter	Included
Low Oil Shutdown	Yes
Neutral Bonded to Ground	Yes
Start Switch Type	Off/Run/Start
Start Switch Location	On Control Panel
Fuel Gauge	Yes
Fuel Tank Capacity gal (L)	7.9 (29.9)
Run Time at 50% (Hours)	11
Handle Style	Dual Grip, Single Folding with Lock Pin
Wheel Type	9.5" Never Flat
Generator Cord Included	25ft / 20A Outdoor, Multi-Outlet with Lighted Power Indicator
Warranty- Residential	3 Year Limited
Warranty- Commercial	1 Year Limited
Included	25ft generator cord, engine oil, handle & wheel kit, battery & charger, owner's manual

Dimensions and Weights

Length in (mm)	27.2 (692)
Width in (mm)	27 (684)
Height in (mm)	26.5 (674)
Extended Length in (mm)	45.5 (1155)
Carton Length in (mm)	28.5 (725)
Carton Width in (mm)	21.7 (551)
Carton Height in (mm)	28.3 (718)
Unit Weight lbs (kg)	198 (90)
Shipping Weight lbs (kg)	220 (99.8)

