GENERAC®

XT8000EFI

Commercial/Residential Portable Generator

Features

- Generac Electronic Fuel Injected (EFI) Engine
 - Effortless Startup, automotive technology allows for easy and reliable starting.
 - Built for Long-Term Storage, engineered to reduce bad gas problems during storage.
 - · Responsive Load Pickups, electronic engine control delivers reliable power.
- True Power™ Technology provides clean, stable power ideal for sensitive electronics, tools and appliances.
- Idle Control reduces noise and conserves fuel for extended run-times.
- Low-oil shutdown automatically safeguards engine from damage.
- PowerBar™ easily monitors power usage.
- Hour meter tracks usage and monitors maintenance cycles.
- Large-capacity steel fuel tank with incorporated fuel gauge provides durability and extended run times.
- Covered outlets provide added protection from the environment and rugged working conditions.
- All-terrain, never flat wheels and fold-down locking handle for reliable portability and compact storage.
- Controlguard™ provides added protection to the control panel.


Model 7162-0 UPC: 696471072709 (EPA/CARB-California)

Model 7162-1 UPC: 696471074505 (EPA/CARB-California/City of LA)



AC Rated Output Running Watts 8000 AC Maximum Output Starting Watts 10000

Control Panel



GENERAC

Specifications

XT8000EFI

| Model (Configuration) | 7162-0 (EPA/CARB - California) 7162-1 (EPA/CARB - California/City of LA) |
|------------------------------------|-----------------------------------------------------------------------------|
| AC Rated Output Running Watts | 8000 |
| AC Maximum Output Starting Watts | 10000 |
| Rated AC Voltage | 120/240 VAC |
| Rated AC Frequency | 60 Hz |
| Rated 120/240 VAC Amperage | 66.6/33.3 |
| Max 120/240 VAC Amperage | 83.3/41.6 |
| Engine Displacement | 459cc |
| Engine Type | Electronic Fuel Injection (EFI) |
| Engine RPM | 3600 |
| Recommended Oil | 10W-30 / SAE 30 |
| Oil Capacity qt (L) | 1.05 (1.0) |
| Lubrication Method | Pressure |
| Automatic Voltage Regulation (AVR) | Yes |
| Fuel Shut Off | On Control Panel |
| Starting Method | Electric Start / Recoil Pull Start |
| Battery Included | Yes |
| Battery Type | Lead Acid (12V DC, 9Ah) |

| D-H DIN- | 000440 |
|------------------------------|-----------------------------------------------------------------------------------|
| Battery Part No. | 0G9449 |
| Battery Dimensions | 5.94" x 2.56" x 3.70" |
| Battery Wall Charger Adapter | Included |
| Low Oil Shutdown | Yes |
| Neutral Bonded to Ground | Yes |
| Start Switch Type | Off/Run/Start |
| Switch Location | On Control Panel |
| Fuel Gauge | Built-in Tank |
| Fuel Tank Capacity gal (L) | 8.0 (30.3) |
| Run Time at 50% (Hours) | 9.5 |
| Handle Style | Single Folding |
| Wheel Type | 10" (254mm) Solid Wheels |
| Warranty- Residential | 2 Year |
| Warranty- Commercial | 1 Year |
| Included | Engine oil, oil funnel, wheel and handle kit, Controlguard™ and Owner's Manual |

Dimensions and Weights

| Length in (mm) | 31.8 (808.5) |
|--------------------------|---------------|
| Width in (mm) | 27.4 (697.1) |
| Height in (mm) | 27.1 (687.7) |
| Extended Length in (mm) | 47.8 (1212.8) |
| Carton Length in (mm) | 33.4 (850) |
| Carton Width in (mm) | 22.8 (580) |
| Carton Height in (mm) | 24.8 (630) |
| Unit Weight lbs (kg) | 216.1 (98) |
| Shipping Weight lbs (kg) | 244.3 (110.8) |

