

PARTS LISTS, SCHEMATIC DIAGRAMS AND WARRANTY
Parts List - Handlebar Assembly - SPRINT[®], PRO and COMMERCIAL

NOTE: Part numbers listed are available through Country Home Products, Inc.

<u>Ref#</u>	<u>Part#</u>	<u>Description</u>	<u>Ref#</u>	<u>Part#</u>	<u>Description</u>
03	143971	Cable, Throttle, Reverse Throw, B&S	110	143901	Knob, Bracket, PTA [™] Lever
04	112381	Washer, Flat, 1/4", USS	112	143881	Lever, PTA [™]
05	113081	Ignition Switch, Key, E/S, w/805 Hardware	113	143891	Bracket, PTA [™] Lever, Handlebar
06	174561	Handlebar, Lower, Black	116	144001	Cable, PTA [™]
07	144641	Bolt, Carriage, 5/16"-18 x 3", GR 2, ZP	117	118691	Nut, Head Engage Cable
08	110761	Nut, Nylon Locking, 5/16"-18	<u>Not Illustrated</u>		
09	147551	Handlebar, Upper, Black	188241		Wire Harness, w/adapter, B&S
	179191	Handlebar, Upper, Black, w/Grip			
10	123361	Bolt, 5/16"-18 x 1-1/4", HCS, GR 5, ZP			
11	174531	Bracket, key switch			
12	110731	Nut, Nylon Locking, 1/4"-20			
13	101451	Bolt, 1/4"-20 x 1-1/2", HHCS, GR 2, ZP			
14	112371	Washer, Flat, #10, USS			
15	143681	Bracket, Cable, Trimmer Head Engage, Handlebar			
17	143671	Stop, Bail Bar			
18	165331	Grip, Handlebar, Foam			
19	143931	Spring, C, .720" OD x .063" Wire, Handlebar Adjuster			
20	143661	Knob, Handlebar, 5/16"-18			
21	191351	Handlebar Adjuster, Inside			
22	143731	Handlebar Adjuster, Outside			
22.1	145801	Handlebar Adjuster Assembly			
23	112141	Cable Tie, Nylon, Black, 7-1/2"			
25	114561	Bolt, 1/4"-20 x 2", HCS, GR 2, ZP			
26	143981	Cable, Trimmer Head Engage			
30	214661	O-Ring			
109	143651	Bail Bar			

Schematic - Handlebar Assembly - SPRINT[®], PRO and COMMERCIAL




061213

Parts List - Axle Assembly - SPRINT[®], PRO and COMMERCIAL

NOTE: Part numbers listed are available through Country Home Products, Inc.

Ref#	Part#	Description
04	112381	Washer, Flat, 1/4", ZP
08	110761	Nut, Nylon Locking, 5/16"-18
49	151401	Bolt, 1/4"-20 x 3/4", Tri-Lobe (PRO, COMMERCIAL)
50	111581	Bolt, 5/16"-18 x 1", HHCS, GR 2, ZP
83	152331	Nut, Nylon Locking, 7/16"-20, Low Profile
84	147611	Wheel, 16", Black Nylon (PRO)
	147601	Wheel, 16", Chrome, Spoke (COMMERCIAL)
	190061	Wheel, 14", Black Resin, 6-Spoke (SPRINT)
101	143621	Arm, PTA [™] Locking
102	143611	Support, PTA [™] Spring
103	121521	Washer, Nylon, Axle, 3/4" x 3/8" x .020 Thick
104	144011	Spring, E, .500" OD x .075", wire
105	143841	Stud, Pivot
108	147501	Axle Assembly
111	143761	Pivot Support Assembly w/Rod

Schematic - Axle Assembly - SPRINT[®], PRO and COMMERCIAL




050919

Parts List - Main Frame Assembly - All Models

NOTE: Part numbers listed are available through Country Home Products, Inc.

<u>Ref#</u>	<u>Part#</u>	<u>Description</u>	<u>Ref#</u>	<u>Part#</u>	<u>Description</u>
04	112381	Washer, Flat, 1/4", USS	66	<u>COMMERCIAL and SELF-PROPELLED Models</u>	
08	110761	Nut, Nylon Locking, 5/16"-18	223821	Engine, 8.25 TQ, B&S, E/S	
12	110731	Nut, Nylon Locking, 1/4"-20	223421	Engine, 8.25 TQ, B&S, E/S, CA	
28	147521	Frame, Drilled, Aluminum, Orange (PRO, COMMERCIAL)	67	114921 Bracket, Belt Retainer	
	190071	Frame, Steel, Orange (SPRINT)	68	118731 Nut, Nylon Locking, 10-24	
	180421	Frame, Drilled, Aluminum, Orange (SELF-PROPELLED)	69	143831 Bracket, Clutch, Deck	
45	180811	Washer, Lock, 3/8"	70	113071 Pulley, Idler #1, 2-1/4" Diameter	
47	111551	Bolt, 3/8"-24 x 3/4", HHCS, GR 2, ZP	71	143521 Rod, Brake Connecting	
49	151401	Screw, 1/4"-20 x 3/4", Tri-Lobe, ZP	72	134431 Bolt, 5/16"-18 x 1-1/2" HCS	
50	111581	Bolt, 5/16"-18 x 1", HHCS, GR 2, ZP	73	143751 Washer, Nylon, .505" ID x 1" OD	
51	143941	Spring, Ext., .50" OD x .063" Wire	74	143601 Stand-off, Clutch Arm	
52	114431	V-Belt, 1/2" x 45", 4L450	75	143581 Arm, Clutch	
53	110751	Nut, Nylon Locking, 3/8"-16	85	146801 Guide, Engine Pulley, Belt (PRO, COMMERCIAL, SELF-PROPELLED)	
54	144091	Pulley, Idler #2, 2-5/8" OD		143821 Guide, Engine Pulley, Belt (Sprint)	
55	143771	Shield, Outer, Lower	98	152501 Bolt, 1/4"-20 x 3/4" HCS	
56	119191	Pulley 4", V-Belt	99	146821 Rod, Debris Guard (PRO, COMMERCIAL)	
58	145221	Screw, 3/8"-16 x 1-1/2", HHCS (PRO, COMMERCIAL)		143791 Rod, Debris Guard (SPRINT)	
60	146811	Clip, Mounting, Inner Lower Shield, (PRO, COMMERCIAL, SELF-PROPELLED)	100	147581 Screw, 10-24 x 1/2", Type B (PRO, COMMERCIAL)	
	143801	Clip, Mounting, Inner Lower Shield, (SPRINT)		144511 Bolt, Carriage, 10-24 x 5/8" (SPRINT – used with item 68)	
61	146781	Shield, Inner, Lower, aluminum (PRO, COMMERCIAL)	107	143781 Debris Guard (SPRINT, PRO, COMMERCIAL)	
	143811	Shield, Inner, Lower, steel (SPRINT)	114	152141 Rivet, Ratchet, 1/4" OD (PRO, COMMERCIAL, SELF-PROPELLED)	
	179511	Shield, Bottom (SELF-PROPELLED)	115	146791 Wear Strip (PRO, COMMERCIAL)	
62	180131	Bolt, 1/4"-20 x 1", Tri-Lobe, ZP	<u>Not Illustrated:</u>		
63	143871	Battery, 12 V, 2.9 Ah		114681 Bolt, 1/4"-20 x 1-1/4" HCS	
64	143861	Pad, Battery, 1.38" x 7.0"		100771 E-Clip, Clutch Cable (PRO, COMMERCIAL, SPRINT)	
65	143851	Clamp, Battery, Plastic		152361 Tool, head locking	
66	<u>PRO and SPRINT Models</u>		<u>Labels</u>		
	224161	Engine, 6.5 TQ, B&S, M/S		127811 Warning, Add Oil	
	224151	Engine, 6.5 TQ, B&S, E/S		136491 Danger	
	223591	Engine, 6.5 TQ, B&S, E/S, CA		148221 Danger Head Rotation	
	223601	Engine, 6.5 TQ, B&S, M/S, CA		148231 Safety Icons	
				148241 Name, TR2 (PRO, COMMERCIAL, SPRINT)	
				153071 PTA (PRO, COMMERCIAL, SPRINT)	
				153081 Bail Bar	
				193201 Start, Key Bracket	

Schematic - Main Frame Assembly - All Models



061212

Parts List - Handlebar Assembly - SELF- PROPELLED


NOTE: Part numbers listed are available through Country Home Products, Inc.

Ref#	Part#	Description
03	143971	Cable, Throttle, Reverse Throw, B&S
04	112381	Washer, Flat, 1/4" USS
05	113081	Ignition Switch, Key, E/S, w/805 Hardware
06	174561	Handlebar, Lower, Black
07	144641	Bolt, Carriage, 5/16"-18 x 3", GR 2, ZP
08	110761	Nut, Nylon Lock, 5/16"-18
09	147551	Handlebar, Upper, Black
09.1	191911	Handlebar, Upper, Black, w/Grip
10	123361	Bolt, 5/16"-18 x 1-1/4", HHCS, GR 5, ZP
11	174531	Bracket, Key Switch, E/S
12	110731	Nut, Nylon Lock, 1/4"-20
13	101451	Bolt, 1/4"-20 x 1-1/2", HHCS, GR 2, ZP
14	112371	Washer, Flat, #10, USS
15	143681	Bracket, Cable, Trimmer Head Engage, Handlebar
16	189721	Bail Bar
17	143671	Stop, Bail Bar
18	190471	Grip, Handlebar, Textured Vinyl, 18-3/4" Long
19	143931	Spring, C, .720" OD x .063" Wire, Handlebar Adjuster
20	143661	Knob, Handlebar, 5/16"-18
21	191351	Adjuster, Handlebar, Inside
22	143731	Adjuster, Handlebar, Outside
22.1	145801	Adjuster Assembly, Handlebar
23	112141	Tie, Cable, 7-1/2" Long, Black
24	179641	Cable, Transmission
25	114561	Bolt, 1/4"-20 x 2.0", HCS
26	190011	Cable, Trimmer Head Engage
27	179651	Lever, Transmission Engage
28	214661	O-Ring

Not Illustrated:

188241 Wire Harness, w/adaptor

Schematic - Handlebar Assembly - SELF- PROPELLED



061213

CALL TOLL-FREE 1-800-DR-OWNER

Parts List - Axle Assembly - SELF-PROPELLED


NOTE: Part numbers listed are available through Country Home Products, Inc.

<u>Ref#</u>	<u>Part#</u>	<u>Description</u>
01	190531	Cover, Inner, Wheel
02	190541	Sleeve, Axle
04	112381	Washer, Flat, 1/4" USS
08	110761	Nut, Nylon Lock, 5/16"-18
12	110731	Nut, Nylon Lock, 1/4"-20
14	112371	Washer, Flat, #10, USS
46	179581	Belt, Transmission Drive, 3/8" x 20"
50	111581	Bolt, 5/16"-18 x 1" HCS
57	175601	Pulley, Transmission Drive, 2-3/4"
68	118731	Nut, Nylon, Lock, 10-24
76	193801	Transmission, 3 Speeds Forward
77	189791	Ring, Retaining, 10mm x 1" Thick
78	112441	Washer, .50" ID x .75" OD x .125" Thick, Nylon
79	179121	Screw, 1/4"-20 x 1/2", Tri-Lobe
80	213101	Ring, Retaining, .5" Shaft
82	179611	Clutch, Wheel
83	152331	Nut, Nylon, Lock, 7/16"-20, Low Profile
84.1	192381	Wheel Kit, Left, Sub Assembly, w/Item 01
84.2	192371	Wheel Kit, Right, Sub Assembly, w/Item 01
86	193811	Sprocket, Transmission, 10 Tooth
87	189591	Spring, Ext., Transmission Tension
88	179631	Bracket, Anti-Rotation
89	179591	Pulley, Transmission, 4"
90	119831	Bolt, 1/4"-20 x 3/4" HCS
91	179551	Bearing, w/Flange
92	175521	Bolt, Eye, 10-24 x 1/2"
93	193791	Axle, w/Woodruff Key
94	193821	Sprocket, Wheel, 40 tooth
95	179681	Plate, Axle, Mounting, Left
96	180841	Plate, Axle, Mounting, Right
97	179621	Chain, #35, 57 Links plus Master Link
99	213181	Key, Woodruff, 1/8" x 1/2"

Not Illustrated

189581 Key, Woodruff, 5/32" x 5/8"

Schematic - Axle Assembly - SELF-PROPELLED





060328

Parts List - Mow Ball™ Assembly - All Models

NOTE: Part numbers listed are available through Country Home Products, Inc.

<u>Ref#</u>	<u>Part#</u>	<u>Description</u>
14	112371	Washer, Flat, #10 USS
30	213081	Bolt, Flat Head, 5/16"-18 x 2.75" w/Patch
31	143991	Spring, Ext., .500" OD x .049" Wire, Brake Return
32	143511	Brake Arm Assembly
33	121521	Washer, Axle, .750" OD x .380" ID
34	114781	Screw, Pan Head, 10-24 x 5/8", Slotted, GR 2
35	143501	Plate, Bearing, Lower, w/Bearing and Inserts
35.1	164111	Insert, 1/4"-20, Round
36	143491	Plate, Bearing, Upper
37	143921	Bearing, Ball, w/Snap Ring
38	143531	Pulley, V-Belt, 3-1/2"
39	144631	Bolt, 3/8"-16 x 4-3/4", HHCS, GR 5, ZP
40	144101	Mow Ball™, Nylon
41	143571	Plate, Line Spacer
42	143551	Standoff, Line Spacer Plate, T
43	143541	Plate, Back-Up
44	144701	Bolt, Serrated Flange, 5/16"-18 x 3/4", HHCS, GR 5, ZP
118	147181	Bearing Housing Assembly w/Brake and Belt
119	160321	Head Assembly, Complete
REF	145311	Cord, 23" long, .130ml, Orange

Schematic - Mow Ball™ Assembly - All Models



060327