



GROUP EV



EXPLODED VIEW: EV POWER WASHER SM PRO**DRAWING #: 10000031741****GROUP EV**

ITEM	PART#	QTY.	DESCRIPTION
1	10000021318	1	ENGINE 212CC G19 EPA 3 DR
2	0K9902	1	PUMP TRIPLEX
3	0J1445	1	NUT-GARDEN HOSE INLET
4	0H9568	1	COUPLING-FEMALE QDISK
5	0J4188	4	SCREW SHC M8-1.25
6	092479	4	WASHER LOCK M8 RIBBED
7	067989	4	NUT HEX FL WHIZ M8-1.25
8	0H1779	6	SCREW HHFC M8-1.25
9	10000021350	1	ST39 BASE PLATE
10	10000021363	1	DECAL UPPER BILLBOARD 3626 DR
11	0H9617K	1	KIT-NOZZLE
12	0J3079	5	GROMMET-NOZZLE
13	0K6325	4	SCREW BFHSC M6-1.0
14	0L35010ST03	1	BILLBOARD A UPPER BLK
15	0L4068	1	ASSY GUN HOOK
16	0D3700	6	NUT FLANGE M6-1.0 NYLOK
17	10000021309	1	ST39 TUBE HANDLE
18	0L3499	1	HOSE HOOK - WIREFORM
19	0L5458A	1	HOSE
20	0J3374A	1	DECAL QUICK START
21	0J1553	1	DECAL QUICK START
22	0G5442	2	SNAP BUTTON
23	10000026996	1	CRADLE SUB ASSY - SM PRO DR
24	0J2686	2	RING, SNAP
25	022247	4	WASHER FLAT
26	049820	6	NUT HEX LOCK M8-1.25 NY INS
27	10000000165	1	FOOT ASSY - SM PRO
28	0J1443	1	NIPPLE-GARDEN HOSE INLET
29	0H9603	1	AXLE
30	0L3973A	2	WHEEL PNEUM
31	10000020414	1	GUN ASSY DR 4000 PSI
32	0K9900A	1	LANCE ASSY
33	089230	4	SCREW HHFC M8-1.25
34	0J3331	2	SCREW BFHSC M6-1.0
35	0J1444	1	SCREEN-GARDEN HOSE INLET
36	10000020395	1	DECAL GUN 4000 PSI DR

Power Washer Parts Manual





ITEM	PART NO.	QTY.	DESCRIPTION
50	0H95660120	1	OIL CAP
54	0H95660121	1	GASKET
55	0H95660122	4	SCREW
56	0H95660123	1	REAR COVER
62	0K990201010	1	PUMP HEAD ASSEMBLY
66	0H95660125	4	SCREW
71	0J01720110	1	GAS ENGINE FLANGE
79	0H9570	1	THERMIC VALVE
KIT NUMBERS			
KIT A	0J04800118	1	VALVES
KIT B	0H95660111	1	PISTONS
KIT C	0k99020111	1	OIL SEALS
KIT D	0H95660113	1	WATER SEALS
KIT E	0H95660114	1	O-RINGS
KIT F	0H95660115	1	SUPPORT RINGS