

PRODUCT CATALOG

GENERAC®

HOME STANDBY
GENERATORS

PORTABLE
GENERATORS

POWER WASHERS

PRODUCTS
FOR BUSINESS

What is a home standby generator?



A GENERAC HOME STANDBY GENERATOR IS MORE THAN A PRODUCT, IT'S A PROMISE.

You can't put a price on safety and security. When things get complicated, it's good to know that you have a place where you always feel at home. A home standby generator is a promise that your home will always be a home. Generac makes the most reliable home standby generators in the world, so you can focus on those you love the most.



GENERAC HOME STANDBY GENERATORS

Easily maintained and always ready to go, a home standby generator is there to protect you and your family.

22kW
HOME STANDBY
GENERATOR



MOBILE LINK™ REMOTE MONITORING

Free with every Guardian Series Home standby generator, Mobile Link allows you to monitor the status of your generator from anywhere in the world using a smart-phone, tablet, or PC. Easily access information, such as the current operating status and maintenance alerts. Connect your account to your authorized service dealer for fast, friendly and proactive service. With Mobile Link, you are taken care of before the next power outage.



5-YEAR LIMITED WARRANTY

Free with all automatic home standby generators.



ENGINEERED AND BUILT IN THE USA*

Generac generators and engines are engineered and built in the USA.



24/7 CUSTOMER SUPPORT

Standing by all day, every day from our headquarters in Wisconsin to answer any questions you might have.

OTHER HOME STANDBY GENERATORS

	9/8kW	11/10kW	16/16kW	20/18kW	22/19.5kW
Model Number	7029	7031	7035	7038	7042
Engine	Generac G-Force				
Engine Displacement	426cc	530cc	999cc		
Wi-Fi Enabled	Yes				
Quiet-Test Mode	Yes				
db(A) at Exercise	54	58	55	58	59
db(A) at Normal Operating Load	63	64	67		68

*Assembled in the USA using domestic and foreign parts.

GENERAC PORTABLE GENERATORS



GENERAC PORTABLE GENERATORS

Designed and built for the demands of emergency home backup power.



GP8000E
PORTABLE
GENERATOR

COSENSE™
TECHNOLOGY

STOPS. ALERTS. SAVES.

Co-Sense technology provides powerful protection from hazardous carbon monoxide.



3-YEAR LIMITED WARRANTY

Free with all portable generators.



POWERRUSH™ ADVANCED TECHNOLOGY

Delivers 30% more starting capacity allowing you to do more with less.*

OTHER PORTABLE GENERATORS



	GP3600	GP6500	GP6500E	GP8000E
Model Number	7677	7680	7682	7675
Electric Start	No		Yes	
Running/Starting Watts	3600/4500	6500/8125		8000/10000
Co-Sense Technology	No	Yes	No	Yes
PowerRush Advanced Technology	Yes			
Run Time (at 50% load)	9.3 hours	10.5 hours		11 hours

*Increases electrical current upon demand above rated output when starting electric motors.

GENERAC INVERTERS



GENERAC INVERTERS



At home or at the job site, a portable inverter generator will make sure you have power when you need it.

iQ3500
PORTABLE INVERTER
GENERATOR

QUIETER.* SMARTER. BEATS HONDA.



ULTRA QUIET – 40% QUIETER THAN HONDA*

Advanced inverter technology and enclosure design provide optimal quiet performance.



PARALLEL READY

With an optional Parallel Kit, you can connect two portable inverter generators together for twice the power when you need it.



ECONOMY MODE

Automatically adjusts engine speeds to save fuel and reduce sound emissions.

OTHER PORTABLE INVERTER GENERATORS



	GP2200i	GP3000i	GP3500iO	iQ3500
Model Number	7117	7129	7128	7127
Run Volume	Quiet			Ultra Quiet*
Starting Method	Recoil/Pull Start			Electric Start/Recoil
PowerRush Advanced Technology	No	Yes		
Run Time (at 50% load)	7 hours	4.5 hours	8 hours	8.9 hours
Parallel Kit Number	7118	7668		

*Over 5 dB(A) quieter than the eu3000is, based on independent third-party testing.

GENERAC PRESSURE WASHERS



GENERAC PRESSURE WASHERS

Whether you're washing the driveway or prepping for a painting job, you need the right tool.



3100 PSI
PRESSURE WASHER
WITH POWER BROOM
AND SOAP BLASTER



ELECTRIC START

Electric one-touch push start with auto-choke provides reliable, hassle-free startups.



POWERDIAL™

Ergonomic spray gun allows you to easily adjust the power needed between four different tasks – car, wood, concrete and soap – at your fingertips.



GENERAC OHV® ENGINE

Delivers maximum cleaning performance and reliability.

OTHER PRESSURE WASHERS



	2900 PSI	3100 PSI	3100 PSI	3600 PSI
Model Number	6882	6923	7143	6924
Gallons Per Minute (GPM)	2.4		2.5	2.6
Electric Start	No		Yes	No
Accessories Included	Turbo Nozzle, Soap Blaster		Power Broom, Soap Blaster	None
Detergent Tank	1/2 gallon			—
Quick-Change Nozzle Tips	0°, 25°, 40°, Soap			0°, 15°, 25°, 40°, Soap
PowerDial	Yes	No	Yes	No
Warranty	3 Year Limited		2 Year Limited	3 Year Limited

GENERAC WATER PUMPS



GENERAC WATER PUMPS

Our water pumps are designed to offer the most reliable water removal solution for homeowners, construction crews, and more.

2" TRASH WATER PUMP



5-HOUR RUNTIME

Large 3 gallon steel fuel tank with incorporated fuel gauge provides up to 5 hours runtime.



POWERFUL PUMP

Easily pumps up to 158 gallons per minute and solids up to 1".



EASY PRIME

Custom funnel design for quick & easy priming.

OTHER WATER PUMPS



	CW10K	CW20	ST20K	T20S
Model Number	6917	6918	6827	6920
Engine	Generac OHV			Subaru OHC
Run Time	Up to 1 hour	Up to 2 hours	Up to 5 hours	
Max Solids (in.)	—		1/4"	1"
Hose Kit	Yes	No	Yes	
Max Head Discharge (ft.)	100'	108'		98'
Max Suction Lift (ft.)	26'			
Suction Port (in.)	1"	2"		



XC8000E PORTABLE GENERATOR

MODEL #6826

X FRAME - FULLY WRAPPED, HEAVY DUTY 12 GAUGE STEEL TUBE

Provides rugged durability and protects the generator and fuel tank from damage.

STEEL LIFTING POCKET

Designed for easier lifting and transportation on jobsites by crane or forklift.

GENERAC G-FORCE ENGINE 426CC ENGINE

Features Best-in-Class power with full pressure lubrication and is optimized for generator use.



30" BRUSH MOWER

MODEL #AT47030GENG

18.67 HP GENERAC G-FORCE ENGINE

Powerful, easy starting engines make our field and brush mower the natural choice for any task, and are designed for long life.

POWER STEERING

The disc brake system provides power steering. Each wheel is equipped with a hand brake, allowing for easy maneuverability.



3800 PSI BELT-DRIVEN PRESSURE WASHER

MODEL #6712

PRO GRADE ERGONOMIC SPRAY GUN

The easy-to-pull trigger on the spray gun is ideal for longer jobs. This g was designed for reduced fatigue and optimal comfort

BELT DRIVE TRIPLEX PUMP

The heavy-duty belt drive triplex pump lasts three times as long as direct drive pumps. This ensures the unit a reliable choice for whenever you need to pressure wash.



2" TRASH PUMP

MODEL #6920

POWERFUL FOR FAST WATER REMOVAL

This 2" trash pump operates at a rate of 185 gallons of water per minute and can pass solids up to 1" in size. From a small water leak to a massive water emergency, this pump works.

DURABLE DESIGN

This pump has a durable design suitable for any environment. It features a silicon carbide seal, cast iron volute, and impeller.

MMG35

DIESEL GENERATOR



POWERZONE® CONTROLLER

Power Zone provides ultimate control of your generator, with detailed status screens, safety monitoring and alarms and programmability - including remote start.

SUPERSTART™

The MDG35 comes standard with our powerful SUPERSTART alternator for enhanced motor-starting capability.

JOHN DEERE™ ENGINE

Designed to minimize wet-stacking, John Deere FT4 diesel engines include an exhaust temperature management (ETM) system that monitors temperatures and provides supplemental heat when necessary.

MLT6SMD

LIGHT TOWER



DURABLE GENERAC® LEDs

All MLT6 LED light towers feature our robust LED fixtures, designed to last the life of the tower, warranted for 5 years.

POWERZONE® CONTROLLER

Reduce labor and fuel costs with Power Zone light tower controller. Features include programmable auto start and stop and a dusk-to-dawn sensor.

ECOSPEED ENGINE

Our innovative ECOSpeed engine adjusts to power demands, resulting in extreme fuel efficiency and an extended run time of up to 203 hours.



INDUSTRIAL GENERATORS

25kW TO 90mW+ SOLUTIONS WITH EXTENDED
PARALELLING OPTIONS AVAILABLE

DEMAND RESPONSE READY

Certified for both US EPA Stationary Emergency Standby and US EPA Non-Emergency for Demand Response applications.

POWER ZONE PRO SYNC CONTROLLER

Power Zone Pro Sync is the first controller to market with the ability to connect to your industrial generator by the use of Wi-Fi, Bluetooth, and cellular connection. Controller has an intuitive 7" touchscreen for ease of use and ease of readability. Connect with Wi-Fi, Bluetooth, or cellular anywhere, anytime.

SMALL BUSINESS GENERATORS

22kW-150kW SOLUTIONS AVAILABLE

RELIABLE BACKUP POWER

Automatic backup power ensures your home or small business will never be without power.

TRUEPOWER™ TECHNOLOGY

Delivers best-in class power quality with less than 5% total harmonic distortion (THD) for clean, smooth operation of sensitive electronics and appliances.

SMALL FOOTPRINT

May be installed just 18 inches away from a structure, ideal for areas with tight lot lines.





MOBILE LINK™ REMOTE MONITORING SYSTEM

Mobile Link remote monitoring lets you get and share information about your home standby generator no matter where you are, using your computer, smart phone, or mobile device.


Compatible with most 2008-and-newer air-cooled standby generators and 2010-and-newer liquid-cooled standby generators from Generac. Product available in mid-2019.



PARALLEL KITS FOR PORTABLE INVERTER GENERATORS

With an optional Parallel Kit, you can connect two portable inverter generators together for twice the power when needed.

Compatible with GP/iQ portable inverter generators.



MAINTENANCE KITS FOR HOME STANDBY GENERATORS

Scheduled maintenance is a necessity. Our kits offer all the components necessary to perform maintenance on our home standby generators.

Compatible with home standby generators from 7.5kW-22kW.



MAINTENANCE KITS FOR PORTABLE GENERATORS

Scheduled maintenance is a necessity. Our kits offer all the components necessary to perform maintenance on our portable generators.

Compatible with XC/XP/XG/GP portable generators.



50 FT. HOSES FOR PRESSURE WASHERS

For your convenience, Generac offers a variety of specifically designed hoses for use with pressure washers.

Compatible with most pressure washers.



TURBO NOZZLE PRESSURE WASHER NOZZLE

Generac offers a variety of nozzles with quick-change connectors designed for a seamless transition between cleaning projects.

Compatible with most pressure washers.



GENERAC®

WWW.GENERAC.COM

Generac Power Systems, Inc.
S45 W29290 Hwy. 59
Waukesha, WI 53189
1-888-GENERAC (1-888-436-3722)

©2019 Generac Power Systems, Inc. All rights reserved.
Specifications are subject to change without notice.

M193225