

POWERMATE®

PM3000CS

Chipper/Shredder

Model: CSR1030PMNG UPC: 843530007541
(EPA/50 ST)



Features

- **3 in (76.2 mm) chipping capacity:** 2x heavy duty chipping knives slice through branches up to 3 in (76.2 mm) diameter.
- **2.5 Bushel debris collection bag:** Collects shredded debris, keeping the yard clean of waste while providing mulch for flower beds.
- **Oversized hopper:** Four shredding hammers reduce armloads of debris to 1/20th the size.
- **12 in (30.5 cm) Pneumatic wheels:** Large diameter tires and aggressive tread provide increased maneuverability.
- **5.5 HP, 212cc OHV Generac engine:** Easy starting 212cc OHV Generac engine provides 8.85 ft-lbs (11.9 Nm) of gross torque.

PM3000CS

Specifications

Engine	
Displacement	212cc
Power	5.5 HP (4.1 kW)
Torque	8.85 ft-lbs (11.9 Nm)
Starting	Manual
Bore x stroke	70 x 55 mm
Compression ratio	9.0 : 1

Chipping and Shredding	
Maximum chipping diameter	3.0 in (76.2 mm)
Maximum shredding diameter	0.5 in (12.7 mm)
Material reduction	20 :01
Chipper knife (in / mm)	3.54 x 1.46 x 0.35 / 89.9 x 37.1 x 8.89

Unit Dimensions	
Height	44.875 in (113.9 cm)
Width	26.875 in (68.3 cm)
Length	31.875 in (80.9 cm)
Weight	117 lbs (53.1 kg)
Wheels	12 in x 3.25 in (30.5 cm x 8.26 cm)

Packaging	
Packaging dimensions (in / cm)	33.5 x 24 x 24.5 / 85.1 x 61.0 x 62.2
Packaging weight (lbs / kg)	133 / 60.3

Miscellaneous	
Assembly time required	20 minutes
Accessories included	Discharge bag, oil funnel
Controls	Throttle control, ON/OFF switch
Personal protective equipment required	Eye protection, ear protection
USDA Certified spark arrestor	Yes
Warranty	2 year limited